

PlanetPac GmbH

Bachstraße 6
 Telefon +49 40 88 16 22 0 -0
 Internet www.planetpac.de

D – 22885 Barsbüttel
 Telefax +49 40 88 16 22 0-15
 E-Mail info@planetpac.de



Clipempfehlungen high barrier Gewürze (b/bs)

Stand: 06.06.2017

Flachbreite	Nennkaliber	Füllkaliber	Füllrohr- durchmesser	Poly-Clip	Tipper Tie	Poly-Clip	Tipper Tie	Poly-Clip	Poly-Clip Handklipper	Tipper Tie Handklipper
cm	mm*	mm	mm	ICA 8700 / ICA 8700SL	SV 4800	FCA 3430 - 18	RS 4204	FCA 90 R-ID Clip der Teilungen M, L und XL		
6,0 cm	40	42	24	S8740	Z401	18 / 12	Z 4005			E - 532
6,8 cm	45	47	24	S8740	Z401	18 / 12	Z 4005			E - 532
7,5 cm	50	53	28	S8740	Z401	18 / 12	Z 4005			E - 532
8,3 cm	55	60	28	S8740	Z401	18 / 12	Z 4005			E - 532
9,0 cm	60	63	36	S8744	Z401	18 / 12	Z 4005			E - 532
9,7 cm	63	65	36	S8744	Z401	18 / 13	Z 4005			E - 532
10,3 cm	66	70	36	S8744	Z401	18 / 13	Z 411			E - 532
10,5 cm	70	75	36	S8744	Z401	18 / 13	Z 411			E - 532
11,3 cm	75	80	48	S8744	Z401	18 / 13	Z 411			E - 532
12,0 cm	80	85	48	S8748	Z401	18 / 13	Z 411			E - 542
12,8 cm	85	90	48	S8748	Z401	18 / 13	Z 411			E - 542
13,0 cm	87	92	48	S8748	Z401	18 / 14	Z 411			E - 542
13,5 cm	90	95	48	S8748	Z401	18 / 14	Z 411			E - 542

*Nennkaliber + 5 % = Füllkaliber!

Flachbreite cm	Nennkaliber mm*	Füllkaliber mm	Füllrohr- durchmesser mm	Poly-Clip		Tipper Tie		Poly-Clip	Poly-Clip Handklipper	Tipper Tie Handklipper
				ICA 8700 / ICA 8700SL	SV 4800	FCA 3430 - 18	RS 4204	FCA 90 R-ID Clip der TeilungenM, L und XL		
14,7 cm	95	100	48	S8748	Z411	18 / 14	Z 411			E - 542
15,0 cm	98	103	48	S8748	Z411	18 / 14	Z 411			E - 542
15,2 cm	100	105	60	S854 (nach Umbau)	Z411	18 / 14	Z 411			E - 542
16,0 cm	105	110	60	S854 (nach Umbau)	Z411		Z 411			E - 542
16,8 cm	110	115	60	S854 (nach Umbau)	Z411					E - 542
19,0 cm	125	130	60	S854 (nach Umbau)	Z411					
20,0 cm	130	135	60	S854 (nach Umbau)	Z411					
20,5 cm	135	140	70	S854 (nach Umbau)	Z411					
21,0 cm	140	147	70		Z411					
22,0 cm	147	154	70		Z411					
23,5 cm	150	156	70							
25,0 cm	160	168								
25,9 cm	170	178								

***Nennkaliber + 5 % = Füllkaliber!**

Der äußere Stützring der Bremse muss um 5 mm ausgedreht werden. Bei geschlossener Bremse sollte sich der Darm, gemäß eines Standarddarms, mühelos ziehen lassen.