

PlanetPac GmbH

Bachstraße 6
Telefon +49 40 88 16 22 0 -0
Internet www.planetpac.de

D – 22885 Barsbüttel
Telefax +49 40 88 16 22 0-15
E-Mail info@planetpac.de



Clipempfehlung high barrier Liquids

Stand: 04.04.2019

Flachbreite mm	Nennkaliber mm*	Füllkaliber mm	Füllrohr- durchmesser mm	Poly-Clip ICA 8700 / ICA 8700SL	Tipper Tie SV 4800	Poly-Clip FCA 3430 - 18	Tipper Tie RS 4204	Poly-Clip FCA 90 R-ID Clip der Teilungen M, L und XL	Poly-Clip Handklipper	Tipper Tie Handklipper
60 mm	40	42	24	S8740	Z401	18 / 12	Z 4005			E - 532
68 mm	45	47	24	S8740	Z401	18 / 12	Z 4005			E - 532
75 mm	50	53	28	S8740	Z401	18 / 12	Z 4005			E - 532
83 mm	55	60	28	S8740	Z401	18 / 12	Z 4005			E - 532
90 mm	60	63	36	S8740	Z401	18 / 12	Z 4005			E - 532
97 mm	63	65	36	S8740	Z401	18 / 12	Z 4005			E - 532
103 mm	66	70	36	S8740	Z401	18 / 13	Z 411			E - 532
105 mm	70	75	36	S8740	Z401	18 / 13	Z 411			E - 532
113 mm	75	80	48	S8740	Z401	18 / 13	Z 411			E - 532
120 mm	80	85	48	S8744	Z401	18 / 13	Z 411			E - 542
128 mm	85	90	48	S8744	Z401	18 / 13	Z 411			E - 542
130 mm	87	92	48	S8744	Z401	18 / 14	Z 411	L/12,13		E - 542
135 mm	90	95	48	S8744	Z401	18 / 14	Z 411	L/12,13		E - 542
147 mm	95	100	48	S8744	Z411	18 / 14	Z 411	L/12,13		E - 542

*Nennkaliber + 5 % = Füllkaliber!

Flachbreite	Nennkaliber	Füllkaliber	Füllrohr- durchmesser	Poly-Clip	Tipper Tie	Poly-Clip	Tipper Tie	Poly-Clip	Poly-Clip Handklipper	Tipper Tie Handklipper
mm	mm*	mm	mm	ICA 8700 / ICA 8700SL	SV 4800	FCA 3430 - 18	RS 4204	FCA 90 R-ID Clip der TeilungenM, L und XL		
150 mm	98	103	48	S8748	Z411	18 / 14	Z 411	XL/12,13		E - 542
152 mm	100	105	60	S8748	Z411	18 / 14	Z 411	XL/12,13		E - 542
160 mm	105	110	60	S8748	Z411	18 / 14	Z 411	XL/12,13		E - 542
168 mm	110	115	60	S8748	Z411					E - 542
178 mm	115	120	60	S8748	Z411					
183 mm	120	126	60	S854 (nach Umbau)	Z411					
190 mm	125	130	60	S854 (nach Umbau)	Z411					
200 mm	130	135	70	S854 (nach Umbau)	Z411					
205 mm	135	140	70	S854 (nach Umbau)	Z411					
210 mm	140	147	70							
220 mm	147	154	70							
235 mm	150	156	70							
250 mm	160	168								
259 mm	170	178								

*Nennkaliber + 5 % = Füllkaliber!

Der äußere Stützring der Bremse muss um 5 mm ausgedreht werden. Bei geschlossener Bremse sollte sich der Darm, gemäß eines Standarddarms, mühelos ziehen lassen.