

PlanetPac GmbH

Bachstraße 6
Telefon +49 40 88 16 22 0 -0
Internet www.planetpac.de

D – 22885 Barsbüttel
Telefax +49 40 88 16 22 0-15
E-Mail info@planetpac.de



Clipempfehlung high barrier Liquids (b/bs)

Stand: 06.06.2017

Flachbreite	Nennkaliber	Füllkaliber	Füllrohr- durchmesser	Poly-Clip	Tipper Tie	Poly-Clip	Tipper Tie	Poly-Clip	Poly-Clip Handklipper	Tipper Tie Handklipper
cm	mm*	mm	mm	ICA 8700 / ICA 8700SL	SV 4800	FCA 3430 - 18	RS 4204	FCA 90 R-ID Clip der Teilungen M, L und XL		
6,0 cm	40	42	24	S8740	Z401	18 / 12	Z 4005			E - 532
6,8 cm	45	47	24	S8740	Z401	18 / 12	Z 4005			E - 532
7,5 cm	50	53	28	S8740	Z401	18 / 12	Z 4005			E - 532
8,3 cm	55	60	28	S8740	Z401	18 / 12	Z 4005			E - 532
9,0 cm	60	63	36	S8740	Z401	18 / 12	Z 4005			E - 532
9,7 cm	63	65	36	S8740	Z401	18 / 12	Z 4005			E - 532
10,3 cm	66	70	36	S8740	Z401	18 / 13	Z 411			E - 532
10,5 cm	70	75	36	S8740	Z401	18 / 13	Z 411			E - 532
11,3 cm	75	80	48	S8740	Z401	18 / 13	Z 411			E - 532
12,0 cm	80	85	48	S8744	Z401	18 / 13	Z 411			E - 542
12,8 cm	85	90	48	S8744	Z401	18 / 13	Z 411			E - 542
13,0 cm	87	92	48	S8744	Z401	18 / 14	Z 411	L/12,13		E - 542
13,5 cm	90	95	48	S8744	Z401	18 / 14	Z 411	L/12,13		E - 542
14,7 cm	95	100	48	S8744	Z411	18 / 14	Z 411	L/12,13		E - 542

*Nennkaliber + 5 % = Füllkaliber!

Flachbreite	Nennkaliber	Füllkaliber	Füllrohr- durchmesser	Poly-Clip	Tipper Tie	Poly-Clip	Tipper Tie	Poly-Clip	Poly-Clip Handklipper	Tipper Tie Handklipper
cm	mm*	mm	mm	ICA 8700 / ICA 8700SL	SV 4800	FCA 3430 - 18	RS 4204	FCA 90 R-ID Clip der TeilungenM, L und XL		
15,0 cm	98	103	48	S8748	Z411	18 / 14	Z 411	XL/12,13		E - 542
15,2 cm	100	105	60	S8748	Z411	18 / 14	Z 411	XL/12,13		E - 542
16,0 cm	105	110	60	S8748	Z411	18 / 14	Z 411	XL/12,13		E - 542
16,8 cm	110	115	60	S8748	Z411					E - 542
17,8 cm	115	120	60	S8748	Z411					
18,3 cm	120	126	60	S854 (nach Umbau)	Z411					
19,0 cm	125	130	60	S854 (nach Umbau)	Z411					
20,0 cm	130	135	70	S854 (nach Umbau)	Z411					
20,5 cm	135	140	70	S854 (nach Umbau)	Z411					
21,0 cm	140	147	70							
22,0 cm	147	154	70							
23,5 cm	150	156	70							
25,0 cm	160	168								
25,9 cm	170	178								

*Nennkaliber + 5 % = Füllkaliber!

Der äußere Stützring der Bremse muss um 5 mm ausgedreht werden. Bei geschlossener Bremse sollte sich der Darm, gemäß eines Standarddarms, mühelos ziehen lassen.